SK 25 WT



SEMITOP[®] 2

Antiparallel Thyristor Module

SK 25 WT

Preliminary Data


Features

- Compact Design
- One screw mounting
- Heat transfer and isolation through direct copper bonded aluminium oxide ceramic (DBC)
- Glass passived thyristor chips
- Up to 1600V reverse voltage
- UL recognized, file no. E 63 532


Typical Applications*


- Soft starters
- Light control (studios, theaters...)
- Temperature control


V _{RSM}	V _{RRM} , V _{DRM}	I _{RMS} = 29 A A (full conductio	n)	
V	V	(T _s = 85 °C)		
900	800	SK 25 WT 08		
1300 1200		SK 25 WT 12	SK 25 WT 12	
1700 1600		SK 25 WT 16	SK 25 WT 16	
<u> </u>				
Symbol	Conditions	Values	Units	
RMS	W1C ; sin. 180° ; T _s = 100°		A	
	W1C ; sin. 180° ; T _s = 85°C	29	A	
I _{TSM}	T _{vj} = 25 °C ; 10 ms	320	A	
	T _{vj} = 125 °C ; 10 ms	280	A	
i²t	T _{vj} = 25 °C ; 8,310 ms	510	A²s	
	T _{vj} = 125 °C ; 8,310 ms	390	A²s	
V _T	T _{vj} = 25 °C, I _T = 75 A	max. 2,45	V	
V _{T(TO)}	T _{vj} = 125 °C	max. 1,1	V	
r _T	T _{vj} = 125 °C	max. 20	mΩ	
I _{DD} ;I _{RD}	T_{vj} = 125 °C, V_{RD} = V_{RRM}	max. 8	mA	
t _{gd}	T _{vi} = 25 °C, I _G = 1 A; di _G /dt	= 1 A/µs 1	μs	
t _{gr}	V _D = 0,67 *V _{DRM}	1	μs	
(dv/dt) _{cr}	T _{vi} = 125 °C	1000	V/µs	
(di/dt) _{cr}	T _{vi} = 125 °C; f= 5060 Hz	50	Α/μs	
t _q	T _{vi} = 125 °C; typ.	80	μs	
I _H	T _{vi} = 25 °C; typ. / max.	80 / 150	mA	
I _L	T _{vi} = 25 °C; R _G = 33 Ω ; typ	. / max. 150 / 300	mA	
V _{GT}	T _{vi} = 25 °C; d.c.	min. 2	V	
I _{GT}	T _{vi} = 25 °C; d.c.	min. 100	mA	
V _{GD}	T _{vj} = 125 °C; d.c.	max. 0,25	V	
I _{GD}	T _{vj} = 125 °C; d.c.	max. 3	mA	
R _{th(j-s)}	cont. per thyristor	1,7	K/W	
	sin 180° per thyristor	1,78	K/W	
R _{th(j-s)}	cont. per W1C	0,85	K/W	
_	sin 180° per W1C	0,89	K/W	
T _{vj}		-40 +125	°C	
T _{stg}		-40 +125	°C	
T _{solder}	terminals, 10s	260	°C	
V _{isol}	a. c. 50 Hz; r.m.s.; 1 s / 1 m	in. 3000 / 2500	V~	
M _s	Mounting torque to heatsin	2,5	Nm	
M _t			Nm	
а			m/s²	
m		19	g	
Case	SEMITOP [®] 2	Т 37		




SK 25 WT










SK 25 WT



* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.