

## SEMiX<sup>®</sup> 3p

### SEMiX453GB17E4p

#### Features


- Homogeneous Si
- Trench = Trenchgate technology
  V<sub>CE(sat)</sub> with positive temperature
- coefficient
- High short circuit capability
- Press-fit pins as auxiliary contactsUL recognized, file no. E63532
- OL recognized, me no. Lossaz

### **Typical Applications\***

- AC inverter drives
- UPS
- Renewable energy systems

### Remarks

- Product reliability results are valid for  $T_{j=150^{\circ}C}$
- V<sub>isol</sub> between temperature sensor and power section is only 2500V
- For storage and case temperature with TIM see document "TP(\*) SEMiX 3p"



Absolute	e Maximum Ratin	gs		
Symbol	Conditions		Values	Unit
IGBT				
V <sub>CES</sub>	T <sub>j</sub> = 25 °C		1700	V
lc	T <sub>j</sub> = 175 °C	T <sub>c</sub> = 25 °C	731	Α
		T <sub>c</sub> = 80 °C	555	А
I <sub>Cnom</sub>			450	А
I <sub>CRM</sub>	$I_{CRM} = 3 x I_{Cnom}$		1350	Α
V <sub>GES</sub>			-20 20	V
t <sub>psc</sub>	$V_{CC} = 1000 V$ $V_{GE} \le 15 V$ $V_{CES} \le 1700 V$	T <sub>j</sub> = 150 °C	10	μs
Tj			-40 175	°C
Inverse d	liode			
V <sub>RRM</sub>	T <sub>j</sub> = 25 °C		1700	V
l <sub>F</sub>		T <sub>c</sub> = 25 °C	557	Α
	− T <sub>j</sub> = 175 °C	T <sub>c</sub> = 80 °C	412	А
I <sub>Fnom</sub>			450	Α
I <sub>FRM</sub>	$I_{FRM} = 2 x I_{Fnom}$		900	Α
I <sub>FSM</sub>	t <sub>p</sub> = 10 ms, sin 180°, T <sub>j</sub> = 25 °C		2565	Α
Tj			-40 175	°C
Module				•
I <sub>t(RMS)</sub>			600	А
T <sub>stg</sub>	module without TIM		-40 125	°C
Visol	AC sinus 50Hz, t = 1 min		4000	V

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT						
V <sub>CE(sat)</sub>	$I_{\rm C} = 450  {\rm A}$	T <sub>j</sub> = 25 °C		1.90	2.20	V
	V <sub>GE</sub> = 15 V chiplevel	T <sub>j</sub> = 150 °C		2.26	2.45	V
V <sub>CE0</sub>	Chiniavai	T <sub>j</sub> = 25 °C		1.10	1.20	V
		T <sub>j</sub> = 150 °C		1.00	1.10	V
r <sub>CE</sub>	V <sub>GE</sub> = 15 V	T <sub>j</sub> = 25 °C		1.78	2.2	mΩ
	chiplevel	T <sub>j</sub> = 150 °C		2.8	3.0	mΩ
V <sub>GE(th)</sub>	$V_{GE}=V_{CE}$ , $I_{C}$ = 18 mA		5.2	5.8	6.4	V
I <sub>CES</sub>	$V_{GE} = 0 V, V_{CE} = 17$	00 V, T <sub>j</sub> = 25 °C			5	mA
Cies		f = 1 MHz		36.0		nF
C <sub>oes</sub>	$V_{GE} = 0 V$	f = 1 MHz		1.50		nF
C <sub>res</sub>		f = 1 MHz		1.14		nF
$Q_G$	V <sub>GE</sub> = - 8 V+ 15 V			3600		nC
R <sub>Gint</sub>	T <sub>j</sub> = 25 °C			1.7		Ω
t <sub>d(on)</sub>		T <sub>j</sub> = 150 °C		290		ns
t <sub>r</sub>	$I_{\rm C} = 450  {\rm A}$	T <sub>j</sub> = 150 °C		90		ns
Eon	$\Pi_{G \text{ on}} - 2.7 \text{ sz}$	T <sub>j</sub> = 150 °C		131		mJ
t <sub>d(off)</sub>		T <sub>j</sub> = 150 °C		790		ns
t <sub>f</sub>		T <sub>j</sub> = 150 °C		175		ns
E <sub>off</sub>		T <sub>j</sub> = 150 °C		146		mJ
R <sub>th(j-c)</sub>	per IGBT				0.06	K/W
R <sub>th(c-s)</sub>	per IGBT ( $\lambda_{grease}$ =0.81 W/(m*K))			0.029		K/W
R <sub>th(c-s)</sub>	per IGBT, pre-applied phase change material			0.02		K/W



## SEMiX<sup>®</sup> 3p

### SEMiX453GB17E4p

#### **Features**

- Homogeneous Si
- Trench = Trenchgate technology
  V<sub>CE(sat)</sub> with positive temperature
- coefficient
- High short circuit capability
- Press-fit pins as auxiliary contactsUL recognized, file no. E63532
- OL recognized, me no. L00002


### **Typical Applications\***


- AC inverter drives
- UPS
- Renewable energy systems


### Remarks


- Product reliability results are valid for  $T_{j=150^{\circ}C}$
- V<sub>isol</sub> between temperature sensor and power section is only 2500V
- For storage and case temperature with TIM see document "TP(\*) SEMiX 3p"


Characte	eristics					
Symbol	Conditions		min.	typ.	max.	Unit
Inverse d	iode					
$V_F = V_{EC}$	I <sub>F</sub> = 450 A	T <sub>j</sub> = 25 °C		1.98	2.37	V
	V <sub>GE</sub> = 0 V chiplevel	T <sub>j</sub> = 150 °C		2.11	2.52	V
V <sub>F0</sub>	chiplevel	T <sub>j</sub> = 25 °C		1.32	1.56	V
		T <sub>j</sub> = 150 °C		1.08	1.22	V
۲ <sub>F</sub>	chiplevel	T <sub>j</sub> = 25 °C		1.46	1.80	mΩ
		T <sub>j</sub> = 150 °C		2.3	2.9	mΩ
I <sub>RRM</sub>	I <sub>F</sub> = 450 A	T <sub>j</sub> = 150 °C		380		Α
Q <sub>rr</sub>	$di/dt_{off} = 4850 \text{ A/}\mu\text{s}$	T <sub>j</sub> = 150 °C		120		μC
E <sub>rr</sub>	V <sub>GE</sub> = -15 V V <sub>CC</sub> = 900 V	T <sub>j</sub> = 150 °C		72		mJ
R <sub>th(j-c)</sub>	per diode				0.1	K/W
R <sub>th(c-s)</sub>	per diode (λ <sub>grease</sub> =0	.81 W/(m*K))		0.048		K/W
R <sub>th(c-s)</sub>	per diode, pre-applied phase change material			0.038		K/W
Module	·					
L <sub>CE</sub>				20		nH
R <sub>CC'+EE'</sub>	measured per switch	T <sub>C</sub> = 25 °C		1.2		mΩ
		T <sub>C</sub> = 125 °C		1.65		mΩ
Rth <sub>(c-s)1</sub>	calculated without thermal coupling			0.009		K/W
Rth <sub>(c-s)2</sub>	including thermal co Ts underneath mod (m*K))		0.014		K/W	
Rth <sub>(c-s)2</sub>	including thermal control Ts underneath moor phase change mate		0.011		K/W	
Ms	to heat sink (M5)		3		6	Nm
Mt		to terminals (M6)	3		6	Nm
	1					Nm
w					350	g
Temperat	ure Sensor					
R <sub>100</sub>	T <sub>c</sub> =100°C (R <sub>25</sub> =5 kΩ)			493 ± 5%		Ω
B <sub>100/125</sub>	$R_{(T)}=R_{100}exp[B_{100/125}(1/T-1/T_{100})];T[K];$			3550 ±2%		к





























Fig. 8: Typ. switching times vs. gate resistor R<sub>G</sub>






© by SEMIKRON



### SEMiX 3p



### © by SEMIKRON

Rev. 2.0 - 25.01.2017

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

#### **\*IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics

("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.