SKM400GB176DL3

SEMITRANS™ 9

Trench IGBT Modules

SKM400GB176DL3

Features*

- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to 6 x I_{cnom}
- Insulated copper baseplate using aluminum nitride ceramic
- Large clearance (13mm) and creepage distance (20mm), to ground: 50mm

Typical Applications

- AC inverter drives
- Mains 575 – 750 V AC
- Public transport
- Wind power

Remarks

- Terminals 1,4 – 2,5 – 3,6 need to be connected externally



GB

Absolute Maximum Ratings				
Symbol	**Conditions**		**Values**	**Unit**
IGBT				
V_{CES}	T_j = 25 °C		1700	V
I_C	T_j = 150 °C	T_c = 25 °C	442	A
		T_c = 80 °C	314	A
I_{Cnom}			300	A
I_{CRM}			600	A
V_{GES}			-20 ... 20	V
t_{psc}	V_{CC} = 1000 V $V_{GE} \leq$ 20 V $V_{CES} \leq$ 1700 V	T_j = 125 °C	10	µs
T_j			-40 ... 150	°C
Inverse diode				
I_F	T_j = 150 °C	T_c = 25 °C	283	A
		T_c = 80 °C	187	A
I_{FRM}			400	A
I_{FSM}	t_p = 10 ms, sin 180°, T_j = 25 °C		1530	A
T_j			-40 ... 150	°C
Module				
$I_{t(RMS)}$			-	A
T_{stg}			-40 ... 125	°C
V_{isol}	AC sinus 50 Hz, t = 1 min		9500	V

Characteristics						
Symbol	**Conditions**		**min.**	**typ.**	**max.**	**Unit**
IGBT						
$V_{CE(sat)}$	I_C = 300 A V_{GE} = 15 V chiplevel	T_j = 25 °C		1.99	2.45	V
		T_j = 125 °C		2.46	2.90	V
V_{CE0}	chiplevel	T_j = 25 °C		1.00	1.20	V
		T_j = 125 °C		0.90	1.10	V
r_{CE}	V_{GE} = 15 V chiplevel	T_j = 25 °C		3.3	4.2	mΩ
		T_j = 125 °C		5.2	6.0	mΩ
$V_{GE(th)}$	V_{GE}=V_{CE}, I_C = 12 mA		5.2	5.8	6.4	V
I_{CES}	V_{GE} = 0 V V_{CE} = 1700 V	T_j = 25 °C			4	mA
		T_j = 125 °C		-		mA
C_{ies}	V_{CE} = 25 V V_{GE} = 0 V	f = 1 MHz		26.4		nF
C_{oes}		f = 1 MHz		1.10		nF
C_{res}		f = 1 MHz		0.88		nF
Q_G	V_{GE} = - 8 V...+ 15 V			2500		nC
R_{Gint}	T_j = 25 °C			4.9		Ω
$t_{d(on)}$	V_{CC} = 1200 V I_C = 300 A V_{GE} = +15/-15 V $R_{G\ on}$ = 4 Ω $R_{G\ off}$ = 4 Ω di/dt$_{on}$ = 2100 A/µs di/dt$_{off}$ = 2100 A/µs	T_j = 125 °C		933		ns
t_r		T_j = 125 °C		159		ns
E_{on}		T_j = 125 °C		143		mJ
$t_{d(off)}$		T_j = 125 °C		1250		ns
t_f		T_j = 125 °C		150		ns
E_{off}		T_j = 125 °C		109		mJ
$R_{th(j-c)}$	per IGBT				0.072	K/W

SEMITRANS™ 9

Trench IGBT Modules

SKM400GB176DL3

Features*

- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to 6 x I_{cnom}
- Insulated copper baseplate using aluminum nitride ceramic
- Large clearance (13mm) and creepage distance (20mm), to ground: 50mm

Typical Applications

- AC inverter drives
- Mains 575 – 750 V AC
- Public transport
- Wind power

Remarks

- Terminals 1,4 – 2,5 – 3,6 need to be connected externally

Characteristics

Symbol	Conditions		min.	typ.	max.	Unit
Inverse diode						
$V_F = V_{EC}$	I_F = 200 A V_{GE} = 0 V chiplevel	T_j = 25 °C		1.71	2.01	V
		T_j = 125 °C		1.75	2.04	V
V_{F0}	chiplevel	T_j = 25 °C		1.24	1.52	V
		T_j = 125 °C		1.07	1.38	V
r_F	chiplevel	T_j = 25 °C		2.3	2.5	mΩ
		T_j = 125 °C		3.4	3.3	mΩ
I_{RRM}	I_F = 300 A di/dt_{off} = 2100 A/µs V_{GE} = -15 V V_{CC} = 1200 V	T_j = 125 °C		120		A
Q_{rr}		T_j = 125 °C		45		µC
E_{rr}		T_j = 125 °C		22		mJ
$R_{th(j-c)}$	per diode				0.19	K/W
Module						
L_{CE}				-		nH
$R_{CC'+EE'}$	measured per switch	T_C = 25 °C		0.35		mΩ
		T_C = 125 °C		0.5		mΩ
$R_{th(c-s)}$	calculated without thermal coupling (λ_{grease}=0.81 W/(m*K))				0.038	K/W
M_s	to heat sink M6		3		5	Nm
M_t	to terminals	M6	2.5		5	Nm
				-		Nm
w					460	g



GB

 © by SEMIKRON



Fig. 1: Typ. output characteristic, inclusive $R_{CC'+EE'}$



Fig. 2: Rated current vs. temperature $I_C = f(T_C)$



Fig. 3: Typ. turn-on /-off energy = f (I_C)



Fig. 4: Typ. turn-on /-off energy = f (R_G)



Fig. 5: Typ. transfer characteristic



Fig. 6: Typ. gate charge characteristic



Fig. 7: Typ. switching times vs. I_C



Fig. 8: Typ. switching times vs. gate resistor R_G



Fig. 9: Transient thermal impedance



Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'+EE'}$



SEMITRANS 9



GB

This is an electrostatic discharge sensitive device (ESDS) due to international standard IEC 61340.

***IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.

 © by SEMIKRON