

Trench IGBT Modules

SKM400GAL176DL3

Features*


- Trench = Trenchgate technology
- V_{CE(sat)} with positive temperature coefficient
- High short circuit capability, self limiting to 6 x I_{cnom}
- Insulated copper baseplate using aluminum nitride ceramic
- Large clearance (13mm) and creepage distance (20mm), to ground: 50mm

Typical Applications


- AC inverter drives
- Mains 575 750 V AC
- Public transport
- · Wind power

Remarks

 Terminals 1,4 – 2,5 – 3,6 need to be connected externally



Characteristics									
Symbol	Conditions	min.	typ.	max.	Unit				
IGBT	•		•						
V _{CE(sat)}	I _C = 300 A	T _j = 25 °C		1.99	2.45	٧			
	V _{GE} = 15 V chiplevel	T _j = 125 °C		2.46	2.90	٧			
V _{CE0}	chiplevel	T _j = 25 °C		1.00	1.20	V			
		T _j = 125 °C		0.90	1.10	V			
r _{CE}	V _{GE} = 15 V	T _j = 25 °C		3.3	4.2	mΩ			
	chiplevel	T _j = 125 °C		5.2	6.0	mΩ			
$V_{GE(th)}$	$V_{GE}=V_{CE}$, $I_{C}=12$ mA		5.2	5.8	6.4	V			
I _{CES}	V _{GE} = 0 V V _{CE} = 1700 V	T _j = 25 °C			4	mA			
		T _j = 125 °C		-		mA			
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		26.4		nF			
C _{oes}		f = 1 MHz		1.10		nF			
C _{res}		f = 1 MHz		0.88		nF			
Q _G	V _{GE} = - 8 V+ 15 V			2500		nC			
R _{Gint}	T _j = 25 °C		4.9		Ω				





Trench IGBT Modules

SKM400GAL176DL3

Features*

- Trench = Trenchgate technology
- V_{CE(sat)} with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_{cnom}$
- Insulated copper baseplate using aluminum nitride ceramic
- Large clearance (13mm) and creepage distance (20mm), to ground: 50mm


Typical Applications

- · AC inverter drives
- Mains 575 750 V AC
- Public transport
- · Wind power

Remarks

• Terminals 1,4 – 2,5 – 3,6 need to be connected externally

Characte	eristics					
Symbol	Conditions		min.	typ.	max.	Unit
t _{d(on)}	V _{CC} = 1200 V	T _j = 125 °C		933		ns
t _r	I _C = 300 A	T _i = 125 °C		159		ns
Eon	$V_{GE} = +15/-15 \text{ V}$ $R_{G \text{ on}} = 4 \Omega$	T _j = 125 °C		143		mJ
t _{d(off)}	$R_{G \text{ off}} = 4 \Omega$	T _j = 125 °C		1250		ns
t _f	di/dt _{on} = 2100 A/μs	T _j = 125 °C		150		ns
E _{off}	$di/dt_{off} = 2100 \text{ A/}\mu\text{s}$	T _j = 125 °C		109		mJ
R _{th(j-c)}	per IGBT				0.072	K/W
Inverse d	liode					1
$V_F = V_{EC}$	I _F = 200 A	T _j = 25 °C		1.71	2.01	V
	$V_{GE} = 0 V$	T _i = 125 °C		1.75	2.04	V
	chiplevel	*				
V _{F0}	chiplevel	T _j = 25 °C		1.24	1.52	V
		T _j = 125 °C		1.07	1.38	V
r _F	chiplevel	T _j = 25 °C		2.3	2.5	mΩ
	I _F = 300 A	$T_j = 125 ^{\circ}\text{C}$ $T_i = 125 ^{\circ}\text{C}$		3.4	3.3	mΩ
I _{RRM}	di/dt _{off} = 2100 A/μs	,		120		A
Q _{rr}	V _{GE} = -15 V	1] = 125 0		45		μC
Err	V _{CC} = 1200 V	T _j = 125 °C		22		mJ
R _{th(j-c)}	per diode				0.19	K/W
	eling diode	T				
$V_F = V_{EC}$	I _F = 300 A V _{GE} = 0 V	T _j = 25 °C		1.72	2.03	V
	chiplevel	T _j = 125 °C		1.79	2.08	V
V_{F0}	chiplevel	T _j = 25 °C		1.24	1.52	V
		T _j = 125 °C		1.07	1.33	V
r _F	chiplevel	T _j = 25 °C		1.61	1.71	mΩ
		T _j = 125 °C		2.4	2.5	mΩ
I _{RRM}		T _j = 125 °C		145		Α
Q _{rr}	di/dt _{off} = 2100 A/μs V _{GE} = -15 V	T _j = 125 °C		53		μC
E_{rr}	V _{CC} = 1200 V	T _j = 125 °C		26		mJ
R _{th(j-c)}	per diode				0.14	K/W
Module						
L _{CE}				-		nΗ
R _{CC'+EE'}	measured per	T _C = 25 °C		0.35		mΩ
	switch	T _C = 125 °C		0.5		mΩ
R _{th(c-s)}	calculated without t (λ _{grease} =0.81 W/(m*		t.b.d.	0.038	K/W	
Ms	to heat sink M6		3		5	Nm
Mt		M6	2.5		5	Nm
						Nm
W					460	g






Fig. 1: Typ. output characteristic, inclusive R_{CC'+ EE'}




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic









Fig. 6: Typ. gate charge characteristic














This is an electrostatic discharge sensitive device (ESDS) due to international standard IEC 61340.

*IMPORTANT INFORMATION AND WARNINGS

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.

6 Rev. 1.0 − 24.11.2020 © by SEMIKRON