SKN 3F20



Stud Diode

Fast Recovery Rectifier Diode

SKN 3F20

SKR 3F20

Features


- Small recovered charge
- Soft recovery
- Up to 1200 V reverse voltage
- Hermetic metal case with glass
 insulator
- Threaded stud ISO M5 or 10-32 UNF
- SKN: anode to stud SKR: cathode to stud


Typical Applications*


- Inverse diode for power transistor, GTO thyristor, asymmetric thyristor
- SMPS, inverters, choppers
- for severe ambient conditions


V _{RSM}	V _{RRM}	I _{FRMS} = 41 A (maximum value for continuous operation)		
V	V	I _{FAV} = 20 A (sin. 180; 5000 Hz; T _c = 104 °C)		
800	800	SKN 3F20/08	SKR 3F20/08	
800	800	SKN 3F20/08UNF	SKR 3F20/08UNF	
1000	1000	SKN 3F20/10	SKR 3F20/10	
1000	1000	SKN 3F20/10UNF	SKR 3F20/10UNF	
1200	1200	SKN 3F20/12	SKR 3F20/12	
1200	1200	SKN 3F20/12UNF	SKR 3F20/12UNF	


Symbol	Conditions	Values	Units
I _{FAV}	sin. 180; T _c = 85 (100) °C	26 (22)	А
I _{FAV}	K5,5; T _a = 45 °C; sin. 180; 5000 Hz	10	А
I _{FSM}	T _{vi} = 25 °C; 10 ms	375	A
	T _{vi} = 150 °C; 10 ms	310	А
i²t	T _{vi} = 25 °C; 8,3 10 ms	700	A²s
	T _{vj} = 150 °C; 8,3 10 ms	480	A²s
V _F	T _{vi} = 25 °C; I _F = 50 A	max. 2,15	V
V _(TO)	T _{vi} = 130 °C	max. 1,3	V
r _T	T _{vi} = 130 °C	max. 12	mΩ
I _{RD}	$T_{vj} = 25 \text{ °C}; V_{RD} = V_{RRM}$	max. 0,2	mA
I _{RD}	T _{vj} = 130 °C; V _{RD} = V _{RRM}	max. 20	mA
Q _{rr}	T _{vi} = 130 °C, I _F = 50 A,	1,5	μC
I _{RM}	-di/dt = 15 A/µs, V _R = 30 V	5	А
t _{rr}		600	ns
E _{rr}		-	mJ
R _{th(j-c)}		1,2	K/W
R _{th(c-s)}		0,5	K/W
T _{vi}		- 40 + 150	°C
T _{stg}		- 55 + 150	°C
V _{isol}		-	٧~
Ms	to heatsink	1,5	Nm
a		5 * 9,81	m/s²
m	approx.	7	g
Case		E 7	















SKN 3F20



* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.