
# SK 25 KQ



## SEMITOP<sup>®</sup> 1

### Antiparallel Thyristor Module

#### SK 25 KQ

Preliminary Data


#### Features

- Compact Design
- One screw mounting
- Heat transfer and isolation through direct copper bonded aluminium oxide ceramic (DBC)
- Glass passived thyristor chips
- Up to 1600V reverse voltage
- UL recognized, file no. E 63 532


### **Typical Applications**


- Soft starters
- Light control (studios, theaters...)
- Temperature control


V <sub>RSM</sub>		V <sub>RRM</sub> , V <sub>DRM</sub>		I <sub>RMS</sub> = 29 A A (full conduction)	
V		V		(T <sub>s</sub> = 85 °C)	
900		800		SK 25 KQ 08	
1300		1200		SK 25 KQ 12	
1700		1600		SK 25 KQ 16	
Symbol	Cond	litions		Values	Units
I <sub>RMS</sub>	W1C ; sin. 180° ; T <sub>s</sub> = 100°C			20	А
	W1C ;	W1C ; sin. 180° ; T <sub>s</sub> = 85°C		29	А
I <sub>TSM</sub>	T <sub>vi</sub> = 2	5 °C ; 10 ms		320	Α
-	$T_{vi} = 1$	25 °C ; 10 ms		280	А
i²t	$T_{v_i} = 2$	5 °C ; 8,310 ms		510	A²s
	$T_{vj} = 1$	25 °C ; 8,310 ms		390	A²s
V <sub>T</sub>		5 °C, I <sub>T</sub> = 75 A		max. 2,45	V
V <sub>T(TO)</sub>	$T_{v_i} = 1$	25 °C		max. 1,1	V
r <sub>T</sub>	$T_{vj} = 1$	25 °C		max. 20	mΩ
I <sub>DD</sub> ;I <sub>RD</sub>	T <sub>vj</sub> = 125 °C, V <sub>RD</sub> =V <sub>RRM</sub> T <sub>vj</sub> = 25 °C, I <sub>G</sub> = 1 A; di <sub>G</sub> /dt= 1 A/µs		max. 8	mA	
t <sub>gd</sub>	$T_{vj} = 25 \text{ °C}, I_G = 1 \text{ A}; di_G/dt = 1 \text{ A/}\mu\text{s}$			1	μs
t <sub>gr</sub>	$V_{\rm D} = 0.67 \ {}^{*}V_{\rm DRM}$			1	μs
$(dv/dt)_{cr}$ $T_{vi} = 125 \text{°C}$			1000	V/µs	
(di/dt) <sub>cr</sub>	$T_{vi}^{vj} = 1$	25 °C; f= 5060 Hz		50	A/µs
t <sub>q</sub>	$T_{vi} = 1$	25 °C; typ.		80	μs
I <sub>H</sub>	$T_{v_i} = 2$	5 °C; typ. / max.		80 / 150	mA
I <sub>L</sub>	$T_{vj}^{0}$ = 25 °C; R <sub>G</sub> = 33 Ω ; typ. / max.			150 / 300	mA
V <sub>GT</sub>	T <sub>vi</sub> = 2	5 °C; d.c.		min. 2	V
I <sub>GT</sub>	$T_{v_i} = 2$	5 °C; d.c.		min. 100	mA
$V_{GD}$	$T_{vj} = 1$	25 °C; d.c.		max. 0,25	V
I <sub>GD</sub>	T <sub>vj</sub> = 1	25 °C; d.c.		max. 3	mA
R <sub>th(j-s)</sub>	cont. p	er thyristor		1,7	K/W
- 0 - /	sin 18	0° per thyristor		1,78	K/W
R <sub>th(j-s)</sub>	cont. p	er W1C		0,85	K/W
	sin 18	0° per W1C		0,89	K/W
T <sub>vj</sub>				-40 +125	°C
T <sub>stg</sub>				-40 +125	°C
T <sub>solder</sub>	termin	als, 10s		260	°C
V <sub>isol</sub>	a. c. 5	0 Hz; r.m.s.; 1 s / 1 m	nin.	3000 / 2500	V~
M <sub>s</sub>	Mount	ing torque to heatsin	ĸ	1,5	Nm
M <sub>t</sub>					Nm
а					m/s²
m				13	g
Case	SEMIT	OP <sup>®</sup> 1		T 1	




### SK 25 KQ










## SK 25 KQ



This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.