SK 45 STA



SEMITOP[®] 3

Six Separated Thyristors Module

SK 45 STA

Preliminary Data

Features


- Compact design
- One screw mounting
- Heat transfer and isolation through direct copper bonded aluminium oxide ceramic (DCB)
- Glass passivated thyristor chipsUp to 1600 V reverse voltage

Typical Applications*


- Soft starters
- Light control (studios, theatres...)
- Temperature control


V _{RSM}	V _{RRM} , V _{DRM}	I _{TRMS} = 41 A
V	V	(T _s = 75 °C)
900	800	SK 45 STA 08
1300	1200	SK 45 STA 12
1700	1600	SK 45 STA 16


Characteristics		T_h = 25 °C, unless otherwise specified		
Symbol	Conditions	Values	Units	
I _{rms} (W1C)	sin. 180°; T _S = 100°C	33	А	
I _{rms} (W1C)	sin. 180°; T _S = 85°C	47	А	
			А	
I _{TSM} /I _{FSM}	T _{vj} = 25 (125) °C; 10 ms	450 (380)	А	
l²t	T _{vj} = 25 (125) °C; 8,3 10 ms ms	1000 (720)	A²s	
T _{stg}		- 40 + 125	°C	
T _{solder}	terminals, 10 s	260	°C	
Thyristor				
(dv/dt) _{cr}	T _{vi} = 125 °C	1000	V/µs	
(di/dt) _{cr}	T _{vi} = 125 °C; f = 50 60 Hz	50	A/µs	
t _q	$T_{vi}^{,j} = 125 \text{ °C}; \text{ typ.}$	80	μs	
I _H	$T_{vi} = 25 \text{ °C; typ. / max.}$	80 / 150	mA	
IL	T_{vj}^{0} = 25 °C; R _G = 33 Ω; typ. / max.	150 / 300	mA	
V _T	$T_{vi} = 25 \text{ °C}; (I_T = 75 \text{ A}); \text{ max.}$	1,9	V	
V _{T(TO)}	$T_{vi} = 125 ^{\circ}C$	max. 1	V	
r _T	$T_{vi}^{vj} = 125 \text{ °C}$	max. 10	mΩ	
I _{DD} ; I _{RD}	T_{vi}^{vj} = 125 °C; V_{DD} = V_{DRM} ; V_{RD} = V_{RRM}	max. 10	mA	
R _{th(j-s)}		1,2	K/W	
T _{vj}		- 40 + 125	°C	
V _{GT}	T _{vi} = 25 °C; d.c.	3	V	
I _{GT}	$T_{vi}^{vj} = 25 \ ^{\circ}C; \ d.c.$	100	mA	
V _{GD}	$T_{vi} = 125 ^{\circ}C; d.c.$	0,25	V	
I _{GD}	$T_{vi} = 125 \text{ °C; d.c.}$	3	mA	
Diode	vj			
V _F	T _{vi} = °C; (I _F = A); max.		V	
V _(TO)	T _{vi} = °C		V	
r _T	T _{vi} = °C		mΩ	
I _{RD}	$T_{vj} = °C; V_{RD} = V_{RRM}$		mA	
R _{th(j-s)}	1		K/W	
T _{vi}			°C	
Mechanic	al data			
V _{isol}	a.c. 50 Hz; r.m.s.; 1 min / 1s	2500 (3000)	V	
M ₁	mounting torque	2,5	Nm	
w		30	g	
Case	SEMITOP [®] 3			





SK 45 STA













SK 45 STA





This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.