

SEMITOP®4

3-phase bridge rectifier + brake chopper + 3-phase bridge inverter SK 50 DGDL 126 T


Preliminary Data

Features

- One screw mounting module
- Fully compatible with SEMITOP®1,2,3
- Improved thermal performances by aluminium oxide substrate
- Trench IGBT technology
- CAL technology free-wheeling diode
- Integrated NTC temperature sensor

Typical Applications*

- Inverter up to 28 kVA
- Typ. motor power 15 kW





| Absolute Maximum Ratings Ts = 25 °C, unless otherwise specifie | | | | | | | | |
|--|---|------------------|-------|--|--|--|--|--|
| Symbol | Conditions | Values | Units | | | | | |
| IGBT - Inverter. For IGBT chopper maximum ratings, please refer to | | | | | | | | |
| SK35DGD | L126T | | | | | | | |
| V_{CES} | | 1200 | V | | | | | |
| I _C | $T_s = 25 (70) ^{\circ}C$ | 68 (52) | Α | | | | | |
| I _{CRM} | $I_{CRM} = 2 \times I_{Cnom}, t_p = 1 \text{ ms}$ | 100 | Α | | | | | |
| V_{GES} | · | ± 20 | V | | | | | |
| T _j | | -40 + 150 | °C | | | | | |
| Diode - Inverter, Chopper | | | | | | | | |
| I _F | T _s = 25 (70) °C | 62 (46) | Α | | | | | |
| I _{FRM} | $I_{FRM} = 2xI_{Fnom}, t_p = 1 \text{ ms}$ | 100 | Α | | | | | |
| T _j | | -40 + 150 | °C | | | | | |
| Rectifier | | | | | | | | |
| V_{RRM} | | 1600 | V | | | | | |
| I _F | T _s = 70 °C | 61 | Α | | | | | |
| I _{FSM} / I _{TSM} | $t_p = 10 \text{ ms}$, sin 180 ° , $T_j = 25 \text{ °C}$ | 700 | Α | | | | | |
| I ² t | $t_p = 10 \text{ ms}, \sin 180^\circ, T_j = 25^\circ\text{C}$ | 2400 | A²s | | | | | |
| T _j | | -40 + 150 | °C | | | | | |
| T _{sol} | Terminals, 10 s | 260 | °C | | | | | |
| T _{stg} | | -40 + 125 | °C | | | | | |
| V _{isol} | AC, 1 min. / 1 s | 2500 / 3000 | V | | | | | |


| Characte | ristics | s = 25 °C, unless otherwise specified | | | | | | |
|---|---|---------------------------------------|-------------|-------------|-------|--|--|--|
| Symbol | Conditions | min. | typ. | max. | Units | | | |
| IGBT - Inverter. For IGBT chopper electrical characteristics, please refer to | | | | | | | | |
| SK35DGE | | 1 | | | | | | |
| V _{CEsat} | $I_C = 50 \text{ A}, T_j = 25 (125) ^{\circ}\text{C}$ | _ | 1,7 (2) | 2,15 (2,45) | V | | | |
| V _{GE(th)} | $V_{GE} = V_{CE}, I_{C} = 2 \text{ mA}$ | 5 | 5,8 | 6,5 | V | | | |
| V _{CE(TO)} | $T_j = 25 ^{\circ}\text{C} (125) ^{\circ}\text{C}$ | | 1 (0,9) | 1,2 (1,1) | V | | | |
| r _T | $T_{j} = 25 ^{\circ}\text{C} (125) ^{\circ}\text{C}$ | | 14 (22) | 19 (27) | mΩ | | | |
| C _{ies} | $V_{CE} = 25 V_{GE} = 0 V, f = 1 MHz$ | | 3,7 | | nF | | | |
| C _{oes} | $V_{CE} = 25 V_{GE} = 0 V, f = 1 MHz$ | | 0,18 | | nF | | | |
| C _{res} | $V_{CE} = 25 V_{GE} = 0 V, f = 1 MHz$ | | 0,16 | | nF | | | |
| $R_{th(j-s)}$ | per IGBT | | 0,6 | | K/W | | | |
| t _{d(on)} | under following conditions | | 115 | | ns | | | |
| t _r | $V_{CC} = 600 \text{ V}, V_{GE} = \pm 15 \text{ V}$ | | 28 | | ns | | | |
| t _{d(off)} | $I_C = 50 \text{ A}, T_j = 125 \text{ °C}$ | | 509 | | ns | | | |
| t _f | $R_{Gon} = R_{Goff} = 8 \Omega$ | | 100 | | ns | | | |
| E _{on} | inductive load | | 4,6 | | mJ | | | |
| E _{off} | | | 6,3 | | mJ | | | |
| Diode - Inverter, Chopper | | | | | | | | |
| $V_F = V_{EC}$ | I _F = 50 A, T _i = 25(125) °C | | 1,35 (1,35) | | V | | | |
| $V_{(TO)}$ | T _i = 25 °C (125) °C | | 0,95 (0,85) | | V | | | |
| r _T | T _j = 25 °C (125) °C | | 8 (10) | | mΩ | | | |
| $R_{th(j-s)}$ | per diode | | 1 | | K/W | | | |
| I _{RRM} | under following conditions | | 30 | | Α | | | |
| Q_{rr} | $I_F = 50 \text{ A}, V_R = 600 \text{ V}$ | | 10 | | μC | | | |
| E _{rr} | V _{GE} = 0 V, T _j = 125 °C | | 3,6 | | mJ | | | |
| | $di_{F/dt} = 500 \text{ A/}\mu\text{s}$ | | | | | | | |
| Diode - R | ectifier | | | | | | | |
| V_{F} | $I_F = 35 \text{ A}, T_i = 25() ^{\circ}\text{C}$ | | 1,1 | | V | | | |
| V _(TO) | T _i = 150 °C | | 0,8 | | V | | | |
| r _T | T _i = 150 °C | | 11 | | mΩ | | | |
| R _{th(j-s)} | per diode | | 0,9 | | K/W | | | |
| Temperatur sensor | | | | | | | | |
| R _{ts} | 5 %, T _r = 25 (100) °C | | 5000(493) | | Ω | | | |
| Mechanical data | | | | | | | | |
| w | | | 60 | | g | | | |
| M_s | Mounting torque | 2,5 | | 2,75 | Nm | | | |


¹⁾ $V_{ce,sat}$, $V_f = chip level value$


²⁾ For IGBT chopper diagrams please refer to SK35DGDL126T





























This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.