

SEMITOP® 4 Press-Fit

3-phase bridge rectifier + 3-phase bridge inverter

SK25DGD12T4Tp

Features

- · One screw mounting module
- Solder free mounting with Press-Fit terminals
- Fully compatible with other SEMITOP® Press-Fit types
- Improved thermal performances by aluminium oxide substrate
- Trench4 IGBT technology
- CAL4F technology FWD
- Integrated NTC temperature sensor
- UL recognized, file no. E 63 532

Typical Applications*


· Motor drives


Absolute	Maximum Ratir	ngs		
Symbol	Conditions		Values	Unit
IGBT 1	•		•	
V _{CES}	T _j = 25 °C		1200	V
$T_j = 150 ^{\circ}\text{C}$	T 150 °C	T _s = 25 °C	35	Α
	T _s = 70 °C	27	Α	
l _C	T 175 °C	T _s = 25 °C	39	Α
	T _j = 175 °C	T _s = 70 °C	32	Α
I _{Cnom}		<u>, </u>	25	Α
I _{CRM}	$I_{CRM} = 3 \times I_{Cnom}$		75	Α
V _{GES}			-20 20	V
t _{psc}	$V_{CC} = 800 \text{ V}$ $V_{GE} \le 15 \text{ V}$ $V_{CES} \le 1200 \text{ V}$	T _j = 150 °C	10	μѕ
Tj			-40 175	°C

Absolute Maximum Ratings							
Symbol	Conditions		Values	Unit			
Diode 1	•			•			
V_{RRM}	T _j = 25 °C		1600	V			
I _F	T _i = 150 °C	T _s = 25 °C	52	Α			
	1 _j = 150 C	T _s = 70 °C	39	Α			
l _F	T 150°C	T _s = 25 °C	52	Α			
	⊢ T _j = 150 °C	T _s = 70 °C	39	Α			
I _{Fnom}			35	Α			
I _{FSM}	10 ms	T _j = 25 °C	370	Α			
	sin 180°	T _j = 150 °C	270	Α			
i ² t	10 ms, sin 180°	°, T _j = 150 °C	364	A ² s			
T _i			-40 150	°C			

Absolute Maximum Ratings							
Symbol	Conditions		Values	Unit			
Diode 2			•				
V_{RRM}	T _j = 25 °C		1200	V			
l _F	T _i = 150 °C	T _s = 25 °C	29	Α			
	- 1 j = 150 C	T _s = 70 °C	22	Α			
l _F	T _i = 175 °C	T _s = 25 °C	32	Α			
	11 = 173 0	T _s = 70 °C	26	Α			
I _{Fnom}			25	Α			
I _{FRM}	I _{FRM} = 2 x I _{Fnom}		50	Α			
I _{FSM}	10 ms, sin 180°,	T _j = 150 °C	100	Α			
Tj			-40 175	°C			

Absolute Maximum Ratings							
Symbol	Conditions	Values	Unit				
Module			•				
I _{t(RMS)}	T _{terminal} = 100 °C, T _S = 60°C, per pin	40	Α				
T _{stg}		-40 125	°C				
V _{isol}	AC, sinusoidal, t = 1 min	2500	V				





SEMITOP® 4 Press-Fit

3-phase bridge rectifier + 3-phase bridge inverter

SK25DGD12T4Tp

Features


- · One screw mounting module
- Solder free mounting with Press-Fit terminals
- Fully compatible with other SEMITOP® Press-Fit types
- Improved thermal performances by aluminium oxide substrate
- Trench4 IGBT technology
- CAL4F technology FWD
- Integrated NTC temperature sensor
- UL recognized, file no. E 63 532


Typical Applications*

Motor drives

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT 1						•
V _{CE(sat)}	$I_{\rm C} = 25 {\rm A}$	T _j = 25 °C		1.85	2.10	V
	V _{GE} = 15 V chiplevel	T _j = 150 °C		2.25	2.45	V
V _{CE0}	chiplevel	T _j = 25 °C		0.80	0.90	V
		T _j = 150 °C		0.70	0.80	V
r _{CE}	$V_{GE} = 15 \text{ V}$	T _j = 25 °C		42	48	mΩ
	chiplevel	T _j = 150 °C		62	66	mΩ
$V_{GE(th)}$	$V_{GE} = V_{CE}, I_{C} = 0.85$	5 mA	5	5.8	6.5	V
I _{CES}	$V_{GE} = 0 V$	T _j = 25 °C		-	1	mA
	V _{CE} = 1200 V			-		mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		1.43		nF
Coes		f = 1 MHz		0.115		nF
C _{res}		f = 1 MHz		0.085		nF
Q_{G}	V _{GE} = - 8 V+ 15 V			138		nC
R _{Gint}	T _j = 25 °C			0		Ω
t _{d(on)}	V _{CC} = 600 V	T _j = 150 °C		22		ns
t _r	$I_{C} = 25 \text{ A}$ $R_{G \text{ on}} = 19 \Omega$	T _j = 150 °C		19.5		ns
Eon	$R_{G \text{ off}} = 19 \Omega$	T _j = 150 °C		2.27		mJ
t _{d(off)}	$di/dt_{on} = 2825 \text{ A/}\mu\text{s}$	T _j = 150 °C		288		ns
t _f	$di/dt_{off} = 2825 A/\mu s$			77.5		ns
E _{off}	$V_{GE \text{ neg}} = -15 \text{ V}$ $V_{GE \text{ pos}} = 15 \text{ V}$	T _j = 150 °C		2.7		mJ
R _{th(j-s)}	per IGBT			1.1		K/W

Characte	Characteristics							
Symbol	Conditions		min.	typ.	max.	Unit		
Diode 1								
V_{F}	I _F = 35 A	T _j = 25 °C		1.20	1.60	V		
	chiplevel	T _j = 125 °C		1.19	1.56	V		
V_{F0}	chiplevel	T _j = 25 °C		0.88	0.98	V		
	Chipievei	T _j = 125 °C		0.73	0.83	V		
r _F	ahinlayal	T _j = 25 °C		9.2	18	mΩ		
	chiplevel	T _j = 125 °C		13	21	mΩ		
I _{RRM}	I _F = 35 A			-		Α		
Q _{rr}				-		μC		
Err				-		mJ		
R _{th(j-s)}	per Diode	•		1.25		K/W		





SEMITOP® 4 Press-Fit

3-phase bridge rectifier + 3-phase bridge inverter

SK25DGD12T4Tp

Features

- · One screw mounting module
- Solder free mounting with Press-Fit terminals
- Fully compatible with other SEMITOP® Press-Fit types
- Improved thermal performances by aluminium oxide substrate
- Trench4 IGBT technology
- CAL4F technology FWD
- Integrated NTC temperature sensor
- UL recognized, file no. E 63 532


Typical Applications*

Motor drives

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Diode 2						
V_{F}	I _F = 25 A	T _j = 25 °C		2.41	2.74	V
	chiplevel	T _j = 150 °C		2.45	2.79	V
V_{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		44	50	mΩ
	Chipievei	T _j = 150 °C		62	68	mΩ
I _{RRM}		T _j = 150 °C		31.5		Α
Q _{rr}	-{V _{GE} = -15 V	T _j = 150 °C		1.15		μС
E _{rr}		T _j = 150 °C		1.28		mJ
R _{th(j-s)}	per Diode			1.5		K/W

Characteristics						
Symbol	Conditions	min.	typ.	max.	Unit	
Module	Module					
Ms	to heatsink	2.5		2.75	Nm	
w	weight		60		g	

Characteristics							
Symbol	Conditions	min.	typ.	max.	Unit		
Temperature Sensor							
R ₁₀₀	T _r = 100 °C		493 ± 5%		Ω		
B _{100/125}	$R_{(T)} = R_{100} \exp[B_{100/125}(1/T-1/T_{100})]; T[K];$	3550 ±2%		К			






Fig.1 : Typ. Diode1 forward characteristic, incl. $R_{CC'+EE'}$




Fig. 2: Typ. IGBT output characteristic, incl. $R_{CC'+\,EE'}$




Fig. 3: Rated IGBT current vs. temperature $I_C = f(T_S)$




Fig. 4: Typ. turn-on /-off energy = $f(I_C)$




Fig. 5: Typ. turn-on /-off energy = $f(R_G)$









Fig.6:Typ.transfer characteristic














dimensions in mm

tolerance system: ISO 2768-m








Suggested drilled hole diameter for terminal pins in the circuit board:

minimum: 1.575mmtypical: 1.6mmmaximum: 1.625mm

Suggested hole diameter for the mounting pins in the circuit board: 3.6mm

These documets are SEMIKRON properties. SEMIKRON reserves all copyrights. All copying and transmitting of this information requires written permission. For the case of industrial property rights, SEMIKRON reserves all rights.

SEMITOP 4 Press-Fit



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

*IMPORTANT INFORMATION AND WARNINGS

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.