# SKiiP 03AC126V1



MiniSKiiP<sup>®</sup>0

3-phase bridge inverter

#### SKiiP 03 AC 126 V1

Preliminary Data

#### **Features**


- Fast Trench IGBTs
- · Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

#### **Remarks**


- V<sub>CEsat</sub>, V<sub>F</sub> = chip level value
  without T-Sensor


 $T_{S}$  = 25 °C, unless otherwise specified **Absolute Maximum Ratings** Symbol |Conditions Values Units **IGBT - Inverter** 1200 V V<sub>CES</sub> T<sub>s</sub> = 25 (70) °C 16 (15) А  $I_{C}$  $t_p \le 1 \text{ ms}$ 16 А I<sub>CRM</sub>  $V_{GES}$ ± 20 V Τ<sub>j</sub> -40...+150 °C **Diode - Inverter** T<sub>s</sub> = 25 (70) °C 14 (11) А  $I_{F}$  $t_p \le 1 \text{ ms}$ 16 А I<sub>FRM</sub> °C -40...+150  $\mathsf{T}_{\mathsf{j}}$ per power terminal (20 A / spring) 20 А I<sub>tRMS</sub> -40...+125 °C  $T_{op} \le T_{stg}$ T<sub>stg</sub>  $V_{isol}$ AC, 1 min. 2500 V


$ \begin{array}{c} C_{L(10)} & J = 25 \ (125) \ ^{\circ}C \\ C_{ies} & V_{CE} = 25 \ V, \ V_{GE} = 0 \ V, \ f = 1 \ MHz \end{array} $	<b>max.</b> 2,1 (2,4) 6,5 1,2 (1,1) 113 (162)	Units
$ \begin{array}{c c c c c c c c c c c c c c c c c c c $	6,5 1,2 (1,1)	V V mΩ nF
	6,5 1,2 (1,1)	V V mΩ nF
	1,2 (1,1)	V mΩ nF
	,	mΩ nF
$ \begin{array}{ccc} r_{T} & T_{j} = 25 \ (125) \ ^{\circ}\text{C} & 87 \ (138) \\ C_{ies} & V_{CE} = 25 \ V, \ V_{GE} = 0 \ V, \ f = 1 \ \text{MHz} & 0,7 \end{array} $	113 (162)	nF
$C_{\text{oes}}$ $V_{\text{CE}}^{\text{C}} = 25 \text{ V}, \text{ V}_{\text{GE}}^{\text{C}} = 0 \text{ V}, \text{ f} = 1 \text{ MHz}$ 0,1		nF
$C_{res}$ $V_{CE} = 25 V, V_{GE} = 0 V, f = 1 MHz$ 0,1		nF
R <sub>th(j-s)</sub> per IGBT 1,5		K/W
t <sub>d(on)</sub> under following conditions 40		ns
$t_r = V_{CC} = 600 \text{ V}, \text{ V}_{GE} = \pm 15 \text{ V}$ 25		ns
$t_{d(off)}$ $I_{Cnom} = 8 \text{ A}, T_j = 125 \text{ °C}$ 370		ns
$t_f = R_{Gon} = R_{Goff} = 82 \Omega$ 85		ns
E <sub>on</sub> inductive load 0,9		mJ
E <sub>off</sub> 0,9		mJ
Diode - Inverter		
$V_{\rm F} = V_{\rm EC}$ $I_{\rm Fnom} = 8 \text{ A}, T_{\rm i} = 25 (125) ^{\circ}{\rm C}$ 1,9 (2)	2,2 (2,4)	V
$V_{(TO)}$ T <sub>j</sub> = 25 (125) °C 1 (0,8)	1,1 (0,9)	V
$r_{T}$ $T_{i} = 25 (125) °C$ 112 (150)	138 (187)	mΩ
R <sub>th(j-s)</sub> per diode 2,5		K/W
I <sub>RRM</sub> under following conditions 13		Α
$Q_{rr} = 8 A, V_R = 600 V$ 1,6		μC
$E_{rr}$ $V_{GE} = 0 V, T_{i} = 125 °C$ 0,7		mJ
$di_{F}/dt = 480 \text{ Å}/\mu \text{s}$		
Temperature Sensor		
$R_{ts} \qquad \%, T_r = () \ ^{\circ}C \qquad ()$		Ω
Mechanical Data		
m 21,5		g
M <sub>s</sub> Mounting torque 2	2,5	Nm





### SKiiP 03AC126V1

















01-10-2009 LAN

## SKIIP 03AC126V1











Fig. 8 Typ. thermal impedance



### SKiiP 03AC126V1

#### circuit



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

\* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.