

2-pack-integrated intelligent Power System

SKiiP 3614 GB12E4-6DUL

Features

- · Intelligent Power Module
- Integrated current and temperature measurement
- Integrated DC-link measurement
- · Solder free power section
- IGBT4 and CAL4F technology
- $T_{jmax} = 175$ °C
- Safety isolated switching and sensor signals
- Digital signal transmission
- CAN Interface
- 100% tested IPM
- RoHS compliant
- UL file no. E242581

Typical Applications*

- Renewable energies
- Traction
- Elevators
- Industrial drives

Remarks

For further information please refer to SKiiP®4 Technical Explanation


Footnotes

1) With assembly of suitable MKP capacitor per terminal

 $^{2)}$ The specified maximum operation junction temperature T_{vjop} is 150°C

Absolute	Maximum Ratings	3		
Symbol	Conditions		Values	Unit
System	•	'		
V _{CC} 1)	Operating DC link v	voltage	900	V
V _{isol}	DC, t = 1 s, each po	olarity	4300	V
I _{t(RMS)}	per AC terminal, rm	s, sinusoidal current	500	Α
I _{max (peak)}	max. peak current of	of power section	5400	Α
I _{FSM}	$T_j = 175 {}^{\circ}\text{C}, t_p = 10$	ms, sin 180°	16547	Α
l ² t	$T_j = 175 {}^{\circ}\text{C}, t_p = 10$	ms, diode	1369	kA ² s
f _{out}	fundamental output (sinusoidal)	frequency	1	kHz
T _{stg}	storage temperatur	е	-40 85	°C
IGBT				
V _{CES}	T _j = 25 °C		1200	V
Ic	T _i = 175 °C	T _s = 25 °C	4664	Α
	1 j = 175 C	T _s = 70 °C	3792	Α
I _{Cnom}			3600	Α
T _j ²⁾	junction temperature		-40 175	°C
Diode				
V_{RRM}	T _j = 25 °C		1200	V
I _F	T _i = 175 °C	T _s = 25 °C	3558	Α
	1, - 175 C	T _s = 70 °C	2821	Α
I _{Fnom}			3600	Α
T _j ²⁾	junction temperature		-40 175 °	
Driver				
Vs	power supply		19.2 28.8	V
V_{iH}	input signal voltage (high)		V _s + 0.3	V
dv/dt	secondary to primary side		75	kV/μs
f _{sw}	switching frequency	у	5	kHz

Characteristics							
Symbol	Conditions		min.	typ.	max.	Unit	
IGBT							
V _{CE(sat)}	I _C = 3600 A	T _j = 25 °C		2.01	2.26	V	
	at terminal	T _j = 150 °C		2.49	2.69	V	
V_{CE0}		T _j = 25 °C		0.80	0.90	V	
		T _j = 150 °C		0.70	0.80	V	
r _{CE}	at terminal	T _j = 25 °C		0.34	0.38	mΩ	
		T _j = 150 °C		0.50	0.53	mΩ	
E _{on} + E _{off}	I _C = 3600 A	V _{CC} = 600 V		1405		mJ	
	T _j = 150 °C	V _{CC} = 900 V		2520		mJ	
R _{th(j-s)}	per IGBT switch				0.0106	K/W	
R _{th(j-r)}	per IGBT switch				0.004	K/W	





2-pack-integrated intelligent Power System

SKiiP 3614 GB12E4-6DUL

Features

- · Intelligent Power Module
- Integrated current and temperature measurement
- Integrated DC-link measurement
- · Solder free power section
- IGBT4 and CAL4F technology
- $T_{jmax} = 175$ °C
- Safety isolated switching and sensor signals
- Digital signal transmission
- CAN Interface
- 100% tested IPM
- · RoHS compliant
- UL file no. E242581

Typical Applications*

- Renewable energies
- Traction
- Elevators
- Industrial drives


Remarks

For further information please refer to SKiiP®4 Technical Explanation

Footnotes

- 1) With assembly of suitable MKP capacitor per terminal
- $^{2)}$ The specified maximum operation junction temperature T_{vjop} is 150°C

Characte	ristics					
Symbol	Conditions		min.	typ.	max.	Unit
Diode						
$V_F = V_{EC}$	I _F = 3600 A	T _i = 25 °C		2.33	2.65	V
	at terminal	T _i = 150 °C		2.35	2.66	V
V _{F0}		T _i = 25 °C		1.30	1.50	V
		T _i = 150 °C		0.90	1.10	V
r _F		T _i = 25 °C		0.29	0.32	mΩ
	at terminal	T _i = 150 °C		0.40	0.43	mΩ
E _{rr}	I _F = 3600 A	V _R = 600 V		238		mJ
	T _j = 150 °C	V _R = 900 V		300		mJ
R _{th(j-s)}	per diode switch	l			0.0187	K/W
R _{th(j-r)}	per diode switch				0.011	K/W
Driver	1		1			
Vs	supply voltage nor	stabilized	19.2	24	28.8	V
I _{S0}	bias current @V _s =	24V, $f_{sw} = 0$, $I_{AC} = 0$		315		mA
Is	$k_1 = 48 \text{ mA/kHz}, k_2$ $f_{\text{out}} = 50 \text{Hz}, \text{ sinusoid}$	$= 0,000063 \text{ mA/A}^2,$ dal current	= 315	+ k ₁ * f _{sw}	+ k ₂ * l _{AC} ²	mA
V_{IT+}	input threshold vol	tage (HIGH)	0,7*V _s			٧
V _{IT-}	input threshold vol	tage (LOW)			0,3*V _s	V
R _{IN}	input resistance			13		kΩ
C _{IN}	input capacitance			1		nF
t _{pRESET}	error memory reset time			500		ms
t _{pReset(OCP)}	Over current reset	time				μs
t _{TD}	top / bottom switch	interlock time		3		μs
t _{jitter}	jitter clock time			50	58	ns
t _{SIS}	short pulse suppre	ssion time		0.6		μs
t _{POR}	Power-On-Reset of	ompleted			1	S
I _{digiout}	digital output sink ((HALT-signal)	current			16	mA
V _{it+ HALT}	input threshold vol (Low>High)	tage HIGH HALT	0,6*V _s			٧
V _{it-HALT}	input threshold vol (High> Low)	tage LOW HALT			0.4*V _s	٧
t _{d(err)}	Error delay time (fr HALT), (depends of		3		370	μs
I _{TRIPSC}	over current trip le	vel	5400			A _{PEAK}
I _{LL}				n.a.		A _{PEAK}
T _{trip}	over temperature t	rip level	128	135	142	°C
$T_{DriverTrip}$	over temperature F	PCB trip level	113	120	124	°C
V_{DCtrip}	over voltage trip le	vel,	950	980	1010	V
$V_{DCtripLL}$				n.a.		V





2-pack-integrated intelligent Power System

SKiiP 3614 GB12E4-6DUL

Features

- Intelligent Power Module
- Integrated current and temperature measurement
- Integrated DC-link measurement
- · Solder free power section
- IGBT4 and CAL4F technology
- $T_{jmax} = 175$ °C
- Safety isolated switching and sensor signals
- Digital signal transmission
- CAN Interface
- 100% tested IPM
- · RoHS compliant
- UL file no. E242581

Typical Applications*


- Renewable energies
- Traction
- Elevators
- Industrial drives

Remarks

For further information please refer to SKiiP®4 Technical Explanation

Footnotes

- 1) With assembly of suitable MKP capacitor per terminal
- $^{2)}$ The specified maximum operation junction temperature T_{vjop} is 150°C




Characteristics									
Symbol	Conditions	min.	typ.	max.	Unit				
System	System								
t _{d(on)IO}	V _{CC} = 600 V I _C = 3600 A	turn on propagation delay time		2.8		μs			
t _{d(off)IO}	$T_j = 25 ^{\circ}\text{C}$	turn off propagation delay time	3.8		μs				
dV_{CE}/dt_{on}	T _i = 25 °C	$I_C = 0 A$		9		kV/μs			
	$V_{CC} = 600 \text{ V}$	$I_C = 3600 \text{ A}$	3			kV/μs			
dV_{CE}/dt_{off}		$I_C = 3600 \text{ A}$		3		kV/μs			
R _{th(s-a)}	flow rate = 500 m ³ /h, T _a =25°C, 500m above sea level				0.017	K/W			
R _{CC'+EE'}	measured per switch, T _s = 25 °C			0.045		mΩ			
L _{CE}	commutation inductance			3		nH			
Сснс	coupling capacitance secondary to heat sink			8.4		nF			
C _{ps}	coupling capacitance primary to secondary		0.102		nF				
I _{CES} + I _{RD}	V _{GE} = 0 V, V _{CE} = 1200 V, T _j = 25 °C		0.527		mA				
M _{dc}	DC terminals		6		8	Nm			
M _{ac}	AC terminals		13		15	Nm			
w	SKiiP System w/o heat sink			4.84		kg			
Wh	heat sink		9.9		kg				


Isolation coordination acc. to EN 50178 and IEC 61800-5-1	
Maximum grid RMS voltage, line-to-line, grounded delta mains	480V+20%
Installation altitude for maximum grid RMS voltage, line-to-line, grounded delta mains	4000m
Maximum grid RMS voltage, line-to-line, star point grounded mains	480V+20%
Installation altitude for maximum grid RMS voltage, line-to-line, star point grounded mains	8000m
Maximum transient peak voltage between low voltage circuit and mains	1900V
Pollution degree acc. to IEC 60664-1 outside the moulded power section	2
Overvoltage cat. acc. to IEC 60664-1 for mains	III
Overvoltage cat. acc. to UL 840 within mains	I
Overvoltage cat. acc. to UL 840 between mains and ground	III
Overvoltage cat. acc. to UL 840 between mains and low voltage circuit	III
Basic isolation	between heat sink and mains
Reinforced isolation	between low voltage circuit and main
Protection level acc. to IEC 60529	IP00


Environmental conditions acc. to IEC 60721


	Storage	Transportation	Operation stationary use at weather protected locations	Operating ground vehicle installations	Operating ship environment
Climatic conditions	1K2 ₍₁₎	2K2 ₍₁₎	3K3 ₍₁₎	5K1 ₍₁₎	6K1 ₍₁₎
Biological conditions	1B1	2B1	3B1	5B1	6B1
Chemically active substances (excluded: salt spray)	1C2	2C1	3C2	5C2	6C2
Mechanically active substances	181	281	381	581	6S1
Mechanical conditions	1M3	(4)	3M6 ₍₂₎	5M3 ₍₃₎	6M3
Contaminating fluids				5F1	


- (1) expanded temperature range: -40°C / +85°C. Please note: by operation near 85°C the life time of product is reduced.
- (2) 3M7 possible, but due to the mechanic load capacity of external components like DC-Link capacitors limited to 3M6
- (3) 5M3 without impact of foreign bodies, stones
- (4) no declaration due to customer-specific packing














Fig. 6: Transient thermal impedance Zth(j-r)




Fig. 7: Transient thermal impedance Zth(s-a)

	R _{th} [K/W]						
	1 2 3 4 5						
$Z_{th(j-s)}$ I	0,0007	0,0038	0,0042	0,0013	0,0006		
$Z_{th(j-s)}$ D	0,0013	0,0067	0,0074	0,0022	0,0011		
Z _{th(j-r)} I	0,0017	0,0044	0,0026	-0,0035	-0,0012		
$Z_{th(j-r)}$ D	0,0041	0,0035	0,0066	-0,0023	-0,0009		
$Z_{th(s-a)}$	0,0029	0,0090	0,0051	0,0000	0,0000		
	tau [s]						
	1	2	3	4	5		
$Z_{th(j-s)}$ I	3,6500	0,4100	0,0650	0,0090	0,0008		
$Z_{th(j-s)}$ D	3,6500	0,4100	0,0650	0,0090	0,0008		
Z _{th(j-r)} I	0,0110	0,0700	0,2000	44,900	337,00		
$Z_{th(j-r)}$ D	0,0070	0,0620	0,1100	4,2000	20,000		
$Z_{\text{th(s-a)}}$	13,100	73,000	168,000	1,0000	1,0000		

Fig. 8: Coefficients of thermal impedances




Fig. 9: Thermal resistance Rth(s-a) versus flow rate V





Fig. 10: Pressure drop Δp versus flow rate V



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

*IMPORTANT INFORMATION AND WARNINGS

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.